

Purpose

Staircase timer ASO-204 serves to keep switched-ON lighting of staircase, corridor, or any other object for the set time and to switch-OFF this lighting automatically, upon elapse of this set time.


Functioning

Turned ON staircase timer supports the lighting during set time by potentiometer (from 0.5 min. to 10 min.). After passage of set time timer will switch OFF the lighting automatically. After switching OFF the lighting there is possibility to switch it ON again.

Mounting

- 1. Take OFF the power.
- 2. Fix the relay to substrate by 2 screws.
- 3. Connect to the circuit according to the diagram.
- 4. Set the operating time using a flathead screwdriver.

Wiring diagram





ASO-204 can't work with backlit buttons.

Technical data

power supply maximum load current (AC-1) activation delay deactivation delay (adjustable) power consumption terminal

tightening torque working temperature dimensions mounting protection level 21÷27 V AC/DC 16 A <1 s 0.5÷10 min. 0.55 w 2.5 mm² screw terminals (cord) 4.0 mm² screw terminals (wire) 0.5 Nm -25÷50°C 50×67×26 mm surface IP20

Power table

~ ` { ` -	=			
tungsten	halogen	fluorescent	energy-saving	LED
2000 W	1250 W	1000 W	500 W	250 W

The above data are indicative and will heavily depend on the design of a specific receiver (that is especially important for LED bulbs, energy-saving lamps, electronic transformers and pulse power supply units), switching frequency and operating conditions.

For more information visit: www.fif.com.pl.

Warranty

The F&F products are covered by a warranty of the 24 months from the date of purchase. Effective only with proof of purchase. Contact your dealer or directly with us.

CE declaration

F&F Filipowski L.P. declares that the device is in conformity with the essential requirements of The Low Voltage Directive (LVD) 2014/35/EU and the Electromagnetic Compatibility (EMC) Directive 2014/30/UE.

The CE Declaration of Conformity, along with the references to the standards in relation to which conformity is declared, can be found at <u>www.fif.com.pl</u> on the product page.